




Safety

All danger zones are protected from access by the use of barriers, safety doors, enclosures etc. Safety switches are used for monitoring the function of all the guards. All the safety switches are wired to a central terminal box. Light-emitting diodes are integrated in the terminal box to indicate which door or guard is open.



Screening plates



STADLER®

Products for tomorrow's world

STADLER® UK Ltd.

Stoke House, Church Road, Ashford
Kent TN23 1RD
Phone: +44 (0) 1173 702 701
Fax: +44 (0) 1275 399 153
Mobil.: +44 (0) 7974 339 980
Contact: Trevor Smart
UK Sales-Manager
trevor.smart@stadler-engineering.com
www.stadler-engineering.com

STADLER® AMERICA LLC.

P.O. Box 5561
Spartanburg, 29304, South Carolina, USA
Phone: +1 864 463 4352 (ext. 149)
Fax: +1 864 463 4670
Contact: Gerben Nijland
Vice President / America Sales-Manager
gerben.nijland@stadler-usa.com
www.stadler-engineering.com

DKSH Australia Pty. Ltd.

14-17 Dansu Court Hallam VIC 3803
Tel: +61 3 9554 6666
Fax: +61 3 9554 6677
sales.ets@dksh.com
www.resourcerecovery.com.au

Head office Germany

STADLER® Anlagenbau GmbH
Robert-Bosch-Straße 4
88361 Altshausen
Phone: +49 7584 9226-60
Fax: +49 7584 9226-69
info@w-stadler.de
www.w-stadler.de

Innovation

Our product developers have proven their technical expertise and capacity for innovation time and again. STADLER® has received several innovation awards for intelligent sorting solutions. True service only begins when the current project has been delivered; with strong support and service back up. We react quickly and reliably and carry out repairs in record time so that your downtimes are kept to a minimum. Service from STADLER® is based on your operational requirements. For this reason, STADLER® is the right partner for you. Call us – we will provide you with all the information you need for your project.



STADLER®

Engineering at its best



Screening Drums

STADLER® Screening Drums

Classifying a material stream into different particle sizes / Creating a consistent (homogeneous) mix of different materials / Separating composite materials (agglomerates)

STADLER®



Capabilities:

- Classifying a material stream into different particle sizes
- Creating a consistent (homogeneous) mix of different materials
- Separating composite materials (agglomerates)

The material to be screened moves axially through the perforated, rotating drum body. The size of the perforations can be adapted to the screening task by changing perforated plates. In addition to the screening operation, thorough mixing, buffering and loosening up of the material stream are performed and controlled by changes in inclination, speed and various fixtures in the drum body.

Design:

The screening drum consists of a sturdy steel frame (sectional steel) and the drum housing with the respective guide plates for feeding the material, for the residues and screened fraction(s). A hood prevents dust from escaping and is also used for connection to the dust extractor provided on site.

The centrepiece of the screening drum is the rotating drum body. The drum body is made of steel plate and sectional steel. The drum body has welded on and machined travelling rims for its guidance and support.

The drum body is driven using friction wheels which ensure quiet running and eases operational demands on the running rings.

Bearing, drive:

All the drive, support and guide wheels have plastic-coated running surfaces. They allow quiet, smooth running of the screening drum, even at higher speeds, and a long service life of all the driving, supporting and guiding components.

The rotating drum body is radially supported on 4 wheels. Two wheels act as drive wheels and are fitted with gear motors. The other wheels are used to support the drum body and co-rotate freely. All the wheels radially so called supporting the drum are in a tandem arrangement. Each of the wheels is 500 mm in diameter and 140 mm in width.

The drum is axially guided between the axial wheels (Ø 300 mm) which, similarly to the main wheels, are provided with a plastic-coated running ring. The main support bearings are of premium quality and dimensioned so that, given appropriate maintenance, long service life of the screening drum is ensured.



Drum body	3.000 x 12.000	3.000 x 10.000	2.500 x 14.000	2.500 x 12.000	2.500 x 10.000	2.500 x 8.000	2.500 x 6.000	1.800 x 5.000
Total length (mm):	16450	14345	19740	16893	14893	12570	10492	9144
Screen length (mm):	12005	10000	6992 + 6992	12000	10000	8000	6000	5000
Screen diameter (mm):	3000	3000	2500	2500	2500	2500	2500	1800
Total width (mm):	4350	4350	3800	3750	3750	3750	3400	2450
Total height (mm):	3727	3727	3661	3663	3663	3664	3640	2790
Weight (t):	35	33	18 + 18,5	27	24	21,7	16,2	10,3
Inclination (*):	3°	3°	3°	3°	3°	3°	3°	3°
*Throughput (m³/h):	161	135	161	135	112	90	67	56
*Assumption for typical commercial/household waste with a screening grade of 80%								